

2003 Altamar 850

Year:	2003
Model:	Altamar 7'4" X 6'11"
Series:	850
Blower:	1hp 240V motor 6500-103
Board:	850 circuit board with 9.50B eprom Board: 6600-092, Eprom: 6660-279
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	850 2 pump panel, 850 2 pump remote panel Panel: 6600-860, Remote: 6600-861
Pump #1:	2.5hp 2sp 240V 1:30 rotation 6500-261
Pump #2:	2.5hp 1sp 240V 9:00 rotation 6500-263
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-138
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-128
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Built-in Brominator and 24-Hour Circulation Pump #6500-035 Optional CD or UV Ozonator, Mazzei Injector required.
Therapy Jets:	8 Fluidix Intelli-Jet, 6 Mini Intelli-Jet, 2 Pulsator 6000-315 6540-347
Whirlpool:	3 Hydro-Air
Therapy Seat:	12 Fluidix ST, 2 Accu-pressure
Foot Jets:	2 Fluidix Intelli-Jet 6000-315
Air Controls:	5
Diverter:	1 3-way
Air Injectors:	14 Barbed style
Hand Rails:	1 9.5" Handrail: 6570-501, Grommets: 6540-651 (2)
Filter:	MicroClean System #6540-501 75ft ² and #6540-501 50ft ² Standard Filter #6540-490 125ft ²

2003 Cameo 850

Year:	2003		
Model:	Cameo 7'7" X 7'7"		
Series:	850		
Blower:	1hp 240V motor 6500-103		
Board:	850 circuit board with 9.50B eprom Board: 6600-092, Eprom: 6660-279		
Transformer:	240V - 12V 6560-274		
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310		
Panel:	850 2 pump panel, 850 2 pump remote panel Panel: 6600-860, Remote: 6600-861		
Pump #1:	2.5hp 2sp 240V 1:30 rotation 6500-261		
Pump #2:	2.5hp 1sp 240V 9:00 rotation 6500-263		
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-138		
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-128		
Weir Gate:	New style sliding weir gate 6540-882		
Timer:	Electronic Dallas time chip on circuit board 6760-024		
Sanitizer:	240V Laing circulation pump, no standard ozone 6500-035		
Therapy Jets:	5 Fluidix Intelli-Jet, 6000-315	2 Pulsator Jet	
Whirlpool:	2 Hydro-Air		
Therapy Seat:	12 Fluidix ST, 6540-643	2 Accu-Pressure	
Foot Jets:	2 Vertical Intelli-Jet LX, 6000-300	3 Hydro-Air,	4 Accu-Pressure calf jets
Air Controls:	5		
Diverter:	2 3-way		
Air Injectors:	14 barbed style		
Hand Rails:	2 9.5" Rail: 6570-501, Grommets: 6540-651 (4)		
Filter:	MicroClean System #6540-501 75ft ² and #6540-502 50ft ² Standard Filter #6540-490 125ft ²		

2003 Capri 850

Year:	2003
Model:	Capri 5'9" X 7'2"
Series:	850
Blower:	1hp 240V motor 6500-103
Board:	850 circuit board with 9.50B eprom Board: 6600-092, Eprom: 6660-279
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	850 1 pump panel Panel: 6600-865
Pump #1:	2.5hp 2sp 240V 9:00 rotation 6500-260
Pump #2:	N/A
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-138
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-128
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Built-in Brominator and 24-Hour Circulation Pump #6500-035 Optional CD or UV Ozonator, Mazzei Injector required.
Therapy Jets:	3 Fluidix Intelli-Jets 6000-315
Whirlpool:	N/A
Therapy Seat:	2 Accu-Pressure, 10 Fluidix ST, Lounge; 6 Mini Intelli-Jets 2 Pulsator Jets, 1 Fluidix intelli-Jet
Foot Jets:	N/A
Air Controls:	2
Diverter:	1 3-way
Air Injectors:	10 Barbed style
Hand Rails:	1 24" Handrail: 6570-505, Grommets: 6540-652 (2)
Filter:	MicroClean System #6540-501 75ft ² and #6540-502 50ft ² Standard Filter #6540-490 125ft ²

2003 Marin 850

Year:	2003
Model:	Marin 7'4" X 6'7"
Series:	850
Blower:	1hp 240V motor 6500-103
Board:	850 circuit board with 9.50B eprom Board: 6600-092, Eprom: 6660-279
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	850 2 pump panel Panel: 6600-860
Pump #1:	2hp 2sp 240V 1:30 rotation 6500-264
Pump #2:	2hp 1sp 240V 9:00 rotation 6500-266
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-138
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-128
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Built-in Brominator and 24-Hour Circulation pump #6500-035. Optional CD or UV Ozonator, Mazzei Injector required.
Therapy Jets:	5 Fluidix Intelli-Jet 6000-315
Whirlpool:	1 Hydro-Air
Therapy Seat:	2 Accu-Pressure, 10 Fluidix ST, Lounge seats; 6 Mini-Intelli-Jet, 4 Fluidix Intelli-Jet, 2 Accu-Pressure, 2 Pulsator.
Foot Jets:	2 Hydro-Air
Air Controls:	4
Diverter:	2 3-way
Air Injectors:	12 Barbed style
Hand Rails:	N/A
Filter:	MicroClean System #6540-501 75ft ² and #6540-502 50ft ² Standard Filter #6540-490 125ft ²

2003 Maxxus 850

Year:	2003
Model:	Maxxus 9'4" X 7'8"
Series:	850
Blower:	N/A
Board:	850 3-pump with 9.60B eprom Board: 6600-094, Eprom: 6660-281
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	850 3-pump panel, 2 850 3-pump remote panels Panel # 6600-866, Remote #6600-867
Pump #1:	2.5hp 2sp 240V 1:30 rotation 6500-261
Pump #2:	#2-2.5hp 1sp 240V 9:00 rotation, #3-2hp 1sp 240V 3:00 rotation #2: 6500-263, #3: 6500-269
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-138
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-128
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Built-Brominator and 24-Hour Circulation Pump Optional CD or UV Ozonator, Mazzei Injector required.
Therapy Jets:	9 Fluidix Intelli-Jet, 1 Duo Path 6000-315, 6540-310
Whirlpool:	3 Hydro-Air
Therapy Seat:	Accu-Ssage seat; 12 Fluidix Intelli-Jet, 4 Accu-Pressure, Ultra- Pulse seat; 6 Ultra-Pulse, 4 Pulsator
Foot Jets:	6 Vertical Accu-Pressure, 2 Micro-Magna Mini-Intellijet: 6540-344
Air Controls:	7
Diverter:	2 3-way
Air Injectors:	N/A
Hand Rails:	2 9.5" Rail: 6570-501, Grommets: 6540-651 (4)
Filter:	MicroClean System #6540-501 75ft ² and #6540-502 75ft ² Standard Filter #6540-490 125ft ²

2003 Optima 850

Year:	2003
Model:	Optima 7'7" X 7'7"
Series:	850
Blower:	1hp 240V motor 6500-103
Board:	850 circuit board with 9.50B eprom Board: 6600-092, Eprom: 6660-279
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	850 2 pump panel, 850 2 pump remote panel Panel: 6600-860, Remote: 6600-861
Pump #1:	2.5hp 2sp 240V 1:30 rotation 6500-261
Pump #2:	2.5hp 1sp 240V 9:00 rotation 6500-263
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-138
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-128
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Built-in Brominator and 24-Hour Circulation pump #6500-035. Optional CD or UV Ozonator, Mazzei Injector required.
Therapy Jets:	8 Fluidix-Intelli-Jet 6000-315
Whirlpool:	2 Hydro-Air
Therapy Seat:	12 Fluidix ST, 2 Accu-Pressure 6540-643
Foot Jets:	8 vertical Accu-Pressure, 4 Accu-Pressure calf jets
Air Controls:	5
Diverter:	2 3-way
Air Injectors:	14 barbed style
Hand Rails:	2 9.5" Rail: 6570-501, Grommets: 6540-651 (4)
Filter:	MicroClean System, #6540-501 75ft ² and #6540-502 50ft ² Standard Filter #6540-490 125ft ²

2003 Caprio ST Potofino

Year:	2003
Model:	Caprio, Caprio ST 7'4" X 6'7"
Series:	Portofino
Blower:	N/A
Board:	Portofino with 3.53 eprom 6600-086
Transformer:	240V - 12V 6560-274
Heater:	4kW@240V, 1kW@120V, Stainless Steel Tube Heater 6500-063
Panel:	Portofino Panel 6600-833
Pump #1:	1.5hp 2sp 120V 9:00 rotation 6500-293
Pump #2:	120V Laing circulation pump 6500-038
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-068
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator
Therapy Jets:	3 Pro Touch II, 1 Duo Path, 6 Mini-Intelljet Pro Touch II: 6540-161, Duo Path: 6540-310, Mini Intellijet: 6540-347
Whirlpool:	N/A
Therapy Seat:	10 Accu-Pressure
Foot Jets:	3 Vertical Pro Touch II Pro Touch II: 6540-161
Air Controls:	3
Diverter:	1 3-way
Air Injectors:	N/A
Hand Rails:	1 13.5" Handrail: 6570-513, Grommets: 6540-652 (2)
Filter:	Micro-Clean 2 Stage System 6540-501 75 sq ft & 6540-502 50 sq ft

2003 Solo Portofino

Year:	2003
Model:	Solo 4'0" X 5'11"
Series:	Portofino
Blower:	N/A
Board:	Portofino with 3.53 eprom 6600-086
Transformer:	240V - 12V 6560-274
Heater:	4kW@240V, 1kW@120V, Stainless Steel Tube Heater 6500-063
Panel:	Portofino Panel 6600-833
Pump #1:	1.5hp 2sp 120V 12:00 rotation 6500-259
Pump #2:	120V Laing circulation pump 6500-038
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-068
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator
Therapy Jets:	4 Pro Touch II 6540-161
Whirlpool:	N/A
Therapy Seat:	10 Accu-Pressure, 2 Mini-Mag 6540-346
Foot Jets:	6 Pulsator, 2 Accu-Pressure
Air Controls:	3
Diverter:	1 3-way
Air Injectors:	N/A
Hand Rails:	2 8" Curved Handrail: 6570-512, Grommets: 6540-651 (4)
Filter:	90 sq. ft. double hole 6540-487

2003 Tango Portofino

Year:	2003
Model:	Tango 5'1" X 6'8"
Series:	Portofino
Blower:	N/A
Board:	Portofino with 3.53 eprom 6600-086
Transformer:	240V - 12V 6560-274
Heater:	4kW@240V, 1kW@120V, Stainless Steel Tube Heater 6500-063
Panel:	Portofino Panel 6600-833
Pump #1:	1.5hp 2sp 120V 9:00 rotation 6500-293
Pump #2:	120V Laing circulation pump 6500-038
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-068
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator
Therapy Jets:	5 Pro Touch II 6540-161
Whirlpool:	N/A
Therapy Seat:	2 Mini Intellijets, 6 Pro Touch II Mini Intellijet: 6540-347, Pro Touch II: 6540-161
Foot Jets:	4 Pulsator, 1 Pro-Touch
Air Controls:	2
Diverter:	1 3-way
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	Micro-Clean 2 Stage System 6540-501 75 sq ft & 6540-502 50 sq ft

2003 Bahia LX15 Sweetwater

Year:	2003
Model:	Bahia 7'4" X 7'4"
Series:	LX15 Sweetwater
Blower:	N/A
Board:	LX15 Sweetwater with 5.52 eprom 6600-088
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V High Flow Heater 6000-156
Panel:	LX15 2-pump Sweetwater panel 6600-631
Pump #1:	2hp 2sp 240V 9:00 rotation 6500-265
Pump #2:	2hp 1sp 240V 9:00 rotation 6500-266
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-068
Weir Gate:	New style sliding weir gate 6540-883
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator and 24-Hour Circulation Pump #6500-035
Therapy Jets:	4 Mini-SMT 2 Micro-SMT, 2 SMT, 11 Accu-Pressure
Whirlpool:	N/A
Therapy Seat:	4 Mini-SMT 2 Micro-SMT, 2 SMT
Foot Jets:	4 Mini-SMT, 1 Turbo-SMT
Air Controls:	3 Sweetwater
Diverter:	1
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	125 sq. ft. 2.5" hole Double sided 6540-488

2003 Cayman Sweetwater

Year:	2003
Model:	Cayman 84"x84"x36"
Series:	Sweetwater
Blower:	N/A
Board:	LX15 Sweetwater with 3.52eprom 6600-088
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V Stainless Steel Tube Heater 6500-402
Panel:	LX10 1-pump Sweetwater panel 6600-630
Pump #1:	2.5hp 2sp 240V 3:00 rotation 6500-254
Pump #2:	N/A
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-140
Weir Gate:	New style sliding weir gate 6540-883
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator.
Therapy Jets:	6 Mini-SMT 6540-960, 3 SMT 6540-755, 2 Micro-Mini 6540-961,
Whirlpool:	N/A
Therapy Seat:	2 Micro-SMT, Accu-Pressure
Foot Jets:	2 SMT 6540-755
Air Controls:	2 Sweetwater
Diverter:	1 Sweetwater
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	125 sq. ft. 2.5" hole, Double Sided 6540-488

2003

Lagunas Sweetwater

Year:	2003
Model:	Lagunas 79"x88"x34"
Series:	Sweetwater
Blower:	N/A
Board:	LX10 Sweetwater with 3.54 eprom 6600-086
Transformer:	240V - 12V 6560-274
Heater:	4kw Stainless Tube Heater 6500-063
Panel:	LX10 1-pump Sweetwater panel 6600-630
Pump #1:	1.5hp 2sp 120V 3:00 rotation 6500-258
Pump #2:	N/A
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-140
Weir Gate:	New style sliding weir gate 6540-883
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator and 24-Hour circulation Pump #6500-035
Therapy Jets:	2 Micro-SMT 6540-961 , 4 Mini-SMT 6540-960, 1 SMT 6540-755
Whirlpool:	N/A
Therapy Seat:	A; 2 Micro-SMT 6540-961, 9 Accu-Pressure, B; 2 Mini-SMT, 2 SMT
Foot Jets:	N/A
Air Controls:	2 Sweetwater
Diverter:	1 Sweetwater
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	125 sq. ft. 2.5" hole Double Sided 6540-488

2003 Palermo LX15 Sweetwater

Year:	2003
Model:	Palermo 7'6" X 7'6"
Series:	LX15 Sweetwater
Blower:	N/A
Board:	LX15 Sweetwater with 3.52 eprom 6600-088
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V Stainless Steel Tube Heater 6500-402
Panel:	LX15 2-pump Sweetwater panel 6600-631
Pump #1:	2hp 2sp 240V 3:00 rotation 6500-262
Pump #2:	2hp 1sp 240V 9:00 rotation 6500-266
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-070
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked. 6600-068
Weir Gate:	New style sliding weir gate 6540-883
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in Brominator and 24-Hour Circulation Pump #6500-035
Therapy Jets:	6 Micro-SMT 6540-961, 11 Mini-SMT 6540-960, 4 Accu-Pressure, 1 SMT
Whirlpool:	N/A
Therapy Seat:	A; 2 Micro-SMT, 9 Accu-Pressure, B; 2 Mini-SMT, 2 SMT 6540-755
Foot Jets:	1Turbo-SMT
Air Controls:	4 Sweetwater
Diverter:	N/A
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	125 sq. ft. 2.5" hole double sided 6540-488