


SUNDANCE SPAS
PARTS HISTORY

2008



Year:	2008
Model:	Altamar
Size:	81" x 86" x 37.5"
Series:	880
Blower:	1hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.51A Eprom Board: 6600-098, Eprom: 6660-328
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 2-pump main panel; AquaTerrace remote light Panel Panel: 6600-860, Remote: 6600-855
Pump #1:	2.5hp 1sp 240V 9:00 rotation 6500-902
Pump #2	2.5hp 1sp 240V 9:00 rotation 6500-902
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	4 Fluidix Nex, 12 Fluidix ST, 4 Accu-Pressure, 2 Whirlpool, 2 Pulsator, 2 Fluidix Intelli-Jet, 6 Fluidix Reflex
Whirlpool:	3 Whirlpool
Therapy Seat:	2 Vortex, 2 Fluidix Intelli-Jet
Foot Jets:	3 Whirlpool, 2 Accu-Pressure
Air Controls:	5
Diverter:	1 (3-way)
Air Injectors:	14 barbed style
Hand Rails:	1 High quality stainless steel handles Rail: 6570-501, Grommets: 6540-651 (4)
Filter:	MicroClean Plus Filter 6540-507 or Standard Filter 6540-488

Year:	2008
Model:	Burlington (With Circ Pump)
Size:	81" x 86" x 37.5"
Series:	680
Blower:	N/A
Board:	680 Series with 3.56+ Eprom Board 6600-288, Eprom 6660-277
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V stainless steel tube heater 6500-402
Panel:	1-pump 680 panel 6600-651
Pump #1:	2.5hp 2sp 240V 7:00 rotation 6500-768
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style skimmer assembly with floating weir canister 373042
Timer:	Electronic counter on circuit board
Sanitizer:	Laing Circ Pump 6500-035
Therapy Jets:	9 SMT, 12 SMT Micro
Whirlpool:	N/A
Therapy Seats:	8 SMT Mini
Foot Jets:	3 SMT
Air Controls:	2
Diverter:	1
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	50 sq ft 373045

Year:	2008
Model:	Burlington
Size:	81" x 86" x 37.5"
Series:	680
Blower:	N/A
Board:	680 Series with 5.55+ Eprom Board 6600-287, Eprom 6660-276
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V stainless steel tube heater 6500-156
Panel:	1-pump 680 panel 6600-651
Pump #1:	2.5hp 2sp 240V 7:00 rotation 6500-768
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style skimmer assembly with floating weir canister 373042
Timer:	Electronic counter on circuit board
Sanitizer:	Optional Circ Pump
Therapy Jets:	9 SMT, 12 SMT Micro
Whirlpool:	N/A
Therapy Seats:	8 SMT Mini
Foot Jets:	3 SMT
Air Controls:	2
Diverter:	1
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	50 sq ft 373045

Year:	2008
Model:	Camden
Size:	76" x 83" x 33"
Series:	780
Blower:	N/A
Board:	780 Series with 3.56+ Eprom Board 6600-286, Eprom 6660-277
Transformer:	120V - 12V 6560-274
Heater:	4kW@240V, 1kW@120V, stainless steel tube heater 6500-402
Panel:	2007 780 1-pump panel 6600-881
Pump #1:	2.5hp 2sp 240V (pump mount pt# 6000-532) 6500-343
Pump # 2	N/A
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Automatic brominator and 24 hour circ pump 6500-035, Sunzone CD installation ready
Therapy Jets:	2 SMT Micro Adjustable, 2 SMT Fluidix Jets, 6 SMT Mini Jets
Whirlpool:	N/A
Therapy Seat:	9 Accu-Pressure, 2 SMT Micro Adjustable, 1 SMT Jet
Foot Jets:	2 SMT
Air Controls:	4 (with light rings)
Diverter:	1 (with light ring)
Air Injectors:	N/A
Hand Rails:	1 Integral
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Cameo
Size:	89" x 89" x 37.5"
Series:	880
Blower:	1hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.51A Eprom Board: 6600-098, Eprom: 6660-328
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 2-pump main panel; AquaTerrace remote light panel Panel: 6600-860, Remote: 6600-855
Pump #1:	2.5hp 1sp 240V 9:00 rotation 6500-902
Pump #2	2.5hp 1sp 240V 9:00 rotation 6500-902
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	4 Fluidix Nex Jet, 12 Fluidix St, 2 Accu-Pressure, 2 Whirlpool, 2 Pulsator 6 Fluidix-Intelli, 14 Air injector jets with quiet high speed air pump
Whirlpool:	2 Hydro-Air
Therapy Seat:	2 Fluidix Nex Jet, 2 Vortex, 2 Fluidix Intelli-Jet
Foot Jets:	3 Whirlpool, 2 Accu-Pressure
Air Controls:	5
Diverter:	2 (3-way)
Air Injectors:	14 barbed style
Hand Rails:	2 High quality stainless steel handles Rail: 6570-501, Grommets: 6540-651 (4)
Filter:	Micro-Clean Plus Stage System = 6540-501 (75 sq ft) & 6540-502 (50 s Standard Filter = 6540-488 (125 sq ft)

Year:	2008
Model:	Capri
Size:	68" x 82" x 30.5"
Series:	880
Blower:	1.5hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.51A Eprom Board: 6600-098, Eprom: 6660-328
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 1-pump panel Panel: 6600-865
Pump #1:	2.5hp 1sp 240V 6500-902
Pump #2/ Pump #3	N/A
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	3 Fluidix Intelli-Jet (6000-315), 6 Mini Intelli-Jet (6540-347), 1 Vortex (6000-310), 2 Pulsator
Whirlpool:	N/A
Therapy Seat:	10 Fluidix ST (6540-643), 2 Euro (6541-787), 6 Reflex (6541-172)
Foot Jets:	N/A
Air Controls:	2
Diverter:	1 (3-way)
Air Injectors:	12 Barbed style
Hand Rails:	1 High quality stainless steel handles 24" Handrail: 6570-505, Grommets: 6540-652 (2)
Filter:	MicroClean Plus Filter 6540-507 or Standard Filter 6540-488

Year:	2008
Model:	Certa
Size:	81" x 86" x 37.5"
Series:	780
Blower:	N/A
Board:	780 Series with 3.56+ Eprom Board 6600-288, Eprom 6660-277
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V stainless steel tube heater 6500-402
Panel:	2-pump panel 6600-880
Pump #1:	2.5hp 2sp 240V (pump mount pt# 6000-532) 6500-343
Pump #2:	2.5hp 1sp 240V (pump mount pt# 6000-532) 6500-341
Temp Sensor:	Curl'd Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curl'd Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in brominator and 24-hour circulation pump 6500-035 Sunzone CD installation ready
Therapy Jets:	4 SMT Micro , 8 SMT Fluidix, 4 SMT Mini
Whirlpool:	N/A
Therapy Seat:	11 Accu-Pressure, 2 SMT Micro, 3 SMT
Foot Jets:	2 SMT
Air Controls:	4 (with light rings)
Diverter:	1 (with light ring)
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Chelsee
Size:	88" x 88" x 36"
Series:	780
Blower:	N/A
Board:	780 Series with 3.56+ Eprom Board 6600-288, Eprom 6660-277
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V stainless steel tube heater 6500-402
Panel:	780 2-pump panel 6600-880
Pump #1:	2.5hp 2sp 240V (pump mount pt# 6000-532) 6500-343
Pump #2:	2hp 1sp 240V (pump mount pt# 6000-532) 6500-341
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in brominator and 24-hour circulation pump 6500-035 Sunzone CD installation ready
Therapy Jets:	8 SMT Fluidix,
Whirlpool:	N/A
Therapy Seats:	3 SMT, 8 SMT Micro, 11 Accu Pressure
Foot Jets:	1 SMT Turbo, 4 SMT Mini
Air Controls:	4 (with optional light rings)
Diverter:	1 (with optional light ring)
Air Injectors:	N/A
Hand Rails:	1 Integral
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Denali
Size:	78" Round x 36"
Series:	680
Blower:	N/A
Board:	680 Series with 5.55+ Eprom Board 6600-289, Eprom 6660-276
Transformer:	120V - 12V 6560-274
Heater:	1kW@120V, 4kW@240V stainless steel tube heater 6000-338
Panel:	1-Pump 680 panel 6600-652
Pump #1:	1.5hp 2sp 120V 6500-758
Pump #2:	N/A
Temp Sensor:	Curl'd Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curl'd Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style skimmer assembly with floating weir canister 373042
Timer:	Electronic counter on circuit board
Sanitizer:	Ozone ready with factory installed ozone injector
Therapy Jets:	3 SMT, 7 SMT Mini, 8 SMT Micro
Whirlpool:	N/A
Therapy Seats:	N/A
Foot Jets:	1 SMT
Air Controls:	2
Diverter:	1 Divert-a-Jet
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	50 sq ft 373045

Year:	2008
Model:	Dover (formally the Metro)
Size:	69" x 82" x 30.5"
Series:	780
Blower:	N/A
Board:	780 Series with 3.56+ Eprom Board 6600-286, Eprom 6660-277
Transformer:	120V - 12V 6560-274
Heater:	4kW@240V, 1kW@120V, stainless steel tube heater 6500-063
Panel:	780 Series 6600-550
Pump #1:	1.5hp 2sp 120V 6500-345 pump mount pt# 6000-532
Pump #2:	N/A
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-068
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic counter on circuit board
Sanitizer:	Automatic brominator, 24 Hour circ pump 6500-038 Sunzone CD ready
Therapy Jets:	9 Accu-pressure Jets, 6 SMT Fluidix
Whirlpool:	N/A
Therapy Seat:	4 SMT Micro, 5 SMT
Foot Jets:	2 SMT Mini
Air Controls:	2
Diverter:	1 (3-way)
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Hamilton
Size:	92"x 92"x36"
Series:	780
Blower:	N/A
Board:	780 Series with 3.56+ Eprom Board 6600-288, Eprom 6660-277
Transformer:	240V - 12V 6560-274
Heater:	5.5kW 240V stainless steel tube heater 6500-402
Panel:	780 Series 2-pump panel 6600-880
Pump #1:	2.5hp 2sp 240V (pump mount pt# 6000-532) 6500-343
Pump #2:	2hp 1sp 240V (pump mount pt# 6000-532) 6500-341
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style sliding weir gate 6540-883
Timer:	Electronic counter on circuit board
Sanitizer:	Built-in brominator and 24-hour circulation pump 6500-035 Sunzone CD installation ready
Therapy Jets:	12 SMT Fluidix, 11 Accu-Pressure 1 SMT Mini, 3 SMT Jets
Whirlpool:	N/A
Therapy Seats:	12 SMT Micro,
Foot Jets:	2 SMT Mini
Air Controls:	3 (with light rings)
Diverter:	1 (with light ring)
Air Injectors:	N/A
Hand Rails:	1 integrated
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Hartford (With Circ Pump)
Size:	88" x 88" x 36"
Series:	680
Blower:	N/A
Board:	780 Series with 3.56 Eprom 6600-288 Eprom 3.56 # 6660-277
Transformer:	120V - 12V 6560-274
Heater:	5.5 Kw Stainlees Steel Tube #6500-402.
Panel:	680 Series 2 Pump Panel 6600-551
Pump #1:	2.5hp 2sp 230V 6500-343 mount 6000-532
Pump #2:	6500-341 2HP 1 SP 230V mount 6000-532
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style weir gate 6540-901
Timer:	Electronic counter on circuit board
Sanitizer:	Laing 230V Circ Pump 6500-035 Sunzone CD ready
Therapy Jets:	6 DXL Jets 6541-322, 6 DX Jets 6541-201, 10 DVX Jets 6541-435, 9 DL Jets 6541-221
Whirlpool:	1 DST 6541-503
Therapy Seat:	6 DL 6541-221, 4 DX 6541-201
Foot Jets:	N/A
Air Controls:	4
Diverter:	1 (3-way)
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Hartford (Without Circ Pump)
Size:	88" x 88" x 36"
Series:	680
Blower:	N/A
Board:	780 Series with 5.56 Eprom 6600-287 Eprom 5.56 # 6660-284
Transformer:	120V - 12V 6560-274
Heater:	5.5 Kw Stainlees Steel Tube # 6000-156
Panel:	680 Series 2 Pump Panel 6600-551
Pump #1:	2.5hp 2sp 230V 6500-343 mount 6000-532
Pump #2:	6500-341 2HP 1 SP 230V mount 6000-532
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked. 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style weir gate 6540-901
Timer:	Electronic counter on circuit board
Sanitizer:	Sunzone CD ready
Therapy Jets:	6 DXL Jets 6541-322, 6 DX Jets 6541-201, 10 DVX Jets 6541-435, 9 DL Jets 6541-221
Whirlpool:	1 DST 6541-503
Therapy Seat:	6 DL 6541-221, 4 DX 6541-201
Foot Jets:	N/A
Air Controls:	4
Diverter:	1 (3-way)
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Hawthorne (With Circ Pump)
Size:	92" x 92" x 36"
Series:	680
Blower:	N/A
Board:	680 Series with 3.56+ Eprom Board 6600-288, Eprom 6660-277 Board 6600-288, Eprom 6660-277
Transformer:	240V - 12V 6560-274
Heater:	5.5 Kw Stainlees Steel Tube #6500-402.
Panel:	2008 680 2-pump panel 6600-651
Pump #1:	2.5hp 2sp 240V Mount 6500-343 6000-532
Pump # 2	6500-341 2.5Hp 1sp 230V, and Mount 6000-532
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style weir gate 6540-901
Timer:	Electronic counter on circuit board
Sanitizer:	Optional 24 hour circ pump 6500-035, Sunzone CD installation ready
Therapy Jets:	8 DVX Jets 6541-435, 11 DXL Jets 6541-322, 6 DL Jets 6541-221 4 DV Jets 6541-211, 6 DX Jets 6541-201
Whirlpool:	1 DST Jet 6541-503
Therapy Seat:	6 DL Jets 6541-221, 2 DX Jets 6541-201
Foot Jets:	2 DVX Jets 6541-435
Air Controls:	3
Diverter:	1 (with light ring)
Air Injectors:	N/A
Hand Rails:	1 Integral
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Hawthorne (Without Circ Pump)
Size:	92" x 92" x 36"
Series:	680
Blower:	N/A
Board:	680 Series with 5.56 Eprom Circuit Board 6600-287, 5.56+ Eprom 6660-284
Transformer:	240V - 12V 6560-274
Heater:	5.5 Kw Stainlees Steel Tube # 6000-156
Panel:	2008 680 2-pump panel 6600-651
Pump #1:	2.5hp 2sp 240V Mount 6500-343 6000-532
Pump # 2	6500-341 2.5Hp 1sp 230V, and Mount 6000-532
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style weir gate 6540-901
Timer:	Electronic counter on circuit board
Sanitizer:	Sunzone CD installation ready
Therapy Jets:	8 DVX Jets 6541-435, 11 DXL Jets 6541-322, 6 DL Jets 6541-221 4 DV Jets 6541-211, 6 DX Jets 6541-201
Whirlpool:	1 DST Jet 6541-503
Therapy Seat:	6 DL Jets 6541-221, 2 DX Jets 6541-201
Foot Jets:	2 DVX Jets 6541-435
Air Controls:	3
Diverter:	1 (with light ring)
Air Injectors:	N/A
Hand Rails:	1 Integral
Filter:	MicroClean I 6540-501 (75 sq ft) & 6540-502 (50 sq ft) Standard Filter 6540-488 (125 sq ft)

Year:	2008
Model:	Majesta
Size:	81" x 86" x 37.5"
Series:	880
Blower:	1.5hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.51A Eprom Board: 6600-098, Eprom: 6660-328
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 2-pump main panel; AquaTerrace remote light panel Panel: 6600-860, Remote: 6600-855
Pump #1:	2.5hp 1sp 240V 9:00 rotation 6500-902
Pump #2/ Pump #3	2.5hp 1sp 240V 9:00 rotation 6500-902
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	2 Fluidix Nex, 14 Fluidix ST, 2 Whirlpool, 14 Air Injector Jets
Whirlpool:	1 Whirlpool
Therapy Seat:	2 Fluidix Nex, 2 Vortex, 3 Fluidix Intelli-Jet, 6 Fluidix Reflex Jets
Foot Jets:	4 Accu-Pressure, 1 Pro-Touch II
Air Controls:	5
Diverter:	1 (3-way)
Air Injectors:	14 barbed style
Hand Rails:	1 High quality stainless steel handles Rail: 6570-501, Grommets: 6540-651 (4)
Filter:	MicroClean Plus Filter 6540-507 or Standard Filter 6540-488

Year:	2008
Model:	Marin 75" x 91" x 33"
Series:	880
Blower:	1.5hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.51A Eprom Board: 6600-098, Eprom: 6660-328
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 2-pump panel Panel: 6600-860
Pump #1:	2.5hp 1sp 240V 6500-903
Pump #2	2.5hp 1sp 240V 6500-901
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked. 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked. 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	4 Fluidix-Intelli, 6 Mini Intelli, 5 Vortex, 2 Pulsator 6000-315 6540-347
Whirlpool:	1 Hydro-Air
Therapy Seat:	10 Fluidix ST, 2 Accu-Pressure 2 Fluidix Euro 6 Fluidix-Reflex 6540-643 6541-787 6541-172
Foot Jets:	2 Hydro-Air
Air Controls:	5
Diverter:	1 (3-way)
Air Injectors:	12 Barbed style
Hand Rails:	N/A
Filter:	MicroClean Plus Filter 6540-507 or Standard Filter 6540-488

Year:	2008
Model:	Maxxus
Size:	90" x 110" x 41.5"
Series:	880
Blower:	1hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.61A Eprom Board: 6600-155, Eprom: 6660-327
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 2-pump main panel; AquaTerrace remote light panel Panel: 6600-860, Remote: 6600-855
Pump #1:	2.5hp 1sp 240V 1:30 rotation 6500-903
Pump #2/ Pump #3	#2-2.5hp 1sp 240V 9:00 rotation, Part # 6500-902 #3-2.5hp 1sp 240V 9:00 rotation, Part # 6500-902
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	12 Fluidix ST, 4 Fluidix Nex, 4 Pulsator, 4 Accu-Pressure, 7 Fluidix Intelli-Jet, 2 Vortex
Whirlpool:	4 Whirlpool
Therapy Seat:	6 Fluidix Reflex, 2 Fluidix Nex, 2 Pulsator
Foot Jets:	8 Accu-Pressure, 2 Whirlpool
Air Controls:	8
Diverter:	2 (3-way)
Air Injectors:	14 Barbed Injectors
Hand Rails:	2 High quality stainless steel handles Rail: 6570-512, Grommets: 6540-651 (4)
Filter:	MicroClean Plus Filter 6540-507 or Standard Filter 6540-488

Year:	2008
Model:	Optima
Size:	89" x 89" x 37.5"
Series:	880
Blower:	1hp 240V blower motor assembly 6500-148
Board:	880 Series circuit board with 9.51A Eprom Board: 6600-098, Eprom: 6660-328
Transformer:	240V - 12V 6560-274
Heater:	"Smart Heater" - plastic housing with titanium element, 5.5kW, 240V 6500-310
Panel:	880 2-pump main panel; AquaTerrace remote light panel Panel: 6600-860, Remote: 6600-855
Pump #1:	2.5hp 1sp 240V 1:30 rotation 6500-902
Pump #2	2.5hp 1sp 240V 9:00 rotation 6500-902
Temp Sensor:	Boxed end connector, thermistor type, resistance can be checked 6600-167
Hi-Limit:	Boxed end connector, thermistor type, resistance can be checked 6600-168
Weir Gate:	New style sliding weir gate 6540-882
Timer:	Electronic Dallas time chip on circuit board 6760-024
Sanitizer:	Automatic brominator and dynamic flow circulation system Sunzone CD installation ready, circulation/filter pump 6500-907
Therapy Jets:	7 Fluidix Intelli-Jet, 4 Accu-Pressure, 2 Vortex
Whirlpool:	N/A
Therapy Seat:	12 Fluidix ST, 4 Fluidix Nex Jets and 1 Whirlpool
Foot Jets:	8 Accu-Pressure, 1 Whirlpool
Air Controls:	5
Diverter:	2 (3-way)
Air Injectors:	14 barbed style
Hand Rails:	2 High quality stainless steel handles Rail: 6570-501, Grommets: 6540-651 (4)
Filter:	MicroClean Plus Filter 6540-507 or Standard Filter 6540-488

Year:	2008
Model:	Tacoma
Size:	68" x 68" x 31"
Series:	680
Blower:	N/A
Board:	680 Series with 5.55+ Eprom Board 6600-289, Eprom 6660-276
Transformer:	120V - 12V 6560-274
Heater:	1kW@120V, 4kW@240V Stainless steel tube heater 6000-338
Panel:	1-pump 680 panel 6600-652
Pump #1:	1.5hp 2sp 120V 6500-758
Pump #2:	N/A
Temp Sensor:	Curled Finger connector, thermistor type, resistance can be checked 6600-166
Hi-Limit:	Curled Finger connector, thermistor type, resistance can be checked 6600-144
Weir Gate:	New style skimmer assembly with floating weir canister 6540-999
Timer:	Electronic counter on circuit board
Sanitizer:	Ozone ready with factory installed ozone injector
Therapy Jets:	3 SMT,
Whirlpool:	N/A
Therapy Seats:	8 SMT Mini
Foot Jets:	1 SMT
Air Controls:	2
Diverter:	N/A
Air Injectors:	N/A
Hand Rails:	N/A
Filter:	35 sq ft 6000-136